Technical Data Sheet | January 2022

# Neopor® F 2000

## This technical data sheet is also applicable for Neopor<sup>®</sup> F 2000 BMB and Neopor<sup>®</sup> F 2000 Ccycled<sup>™</sup>

#### Application

Neopor<sup>®</sup> F 2000 is an expandable polystyrene granulate and is used for the production of flame-retardant, silvergrey foams with reduced thermal conductivity.

Neopor <sup>⊚</sup> F 2200	For the production of blocks and loose bead applications
Neopor <sup>®</sup> F 2300	For the production of blocks, shape molded parts and loose bead applications
Neopor <sup>⊚</sup> F 2400	For the production of thin walled shape molded parts

#### **Product description**

Expandable polystyrene with infrared reflecting additive (graphite) and polymeric flame retardant in uniform distribution.

Blowing agent: pentane.

The fire behavior of foams made of Neopor® F 2000 corresponds:

EN 13501-1 Klasse E

To comply with these classifications, Neopor® F 2000 must not be mixed with other raw materials.

For further information on fire behavior, please contact your local BASF representative.

#### **Circular economy**

#### Biomass balance – Neopor<sup>®</sup> BMB

100% of the fossil-based raw materials required for the manufacturing of this product were replaced by certified sustainable biomass according to the mass balance approach.

#### ■ ChemCycling – Neopor<sup>®</sup> Ccycled<sup>™</sup>

100% of the fossil-based raw materials required for the manufacturing of this product were replaced by certified sustainable recycled materials according to the mass balance approach.

Both the BMB and the Ccycled<sup>™</sup> products have absolutely identical properties to conventional Neopor® F 2000 in every respect.

Regarding the availability of BMB or Ccycled<sup>™</sup> products, please always contact your BASF representative.

#### Food contact regulations

Foams made from Neopor<sup>®</sup> raw materials are not suitable for direct contact with foodstuffs.

#### **Delivery form**

Neopor® F 2000 is supplied as spherical granules in cardboard containers (octabins) containing 1100kg material.





### Storage

Octabins must be protected from the effects of weather (rain, rising damp, snow, frost, sun) and from damage.

To maintain the desired properties of Neopor® F 2000, the raw material should always be stored in a dry and cool location (below 20 °C) and processed within three months.

The contents of opened containers should be processed within a short time. In the meantime, the plastic bag in the container should be kept well closed.

Stacking of octabins is generally not recommended. In case of stacking octabins under controlled conditions, a strong plywood board must always be placed between the stacked containers.

Octabins that are covered with a plastic hood or shrinkwrapped should never be stacked.

### **Safety instructions**

It should be noted that during storage and processing of Neopor<sup>®</sup> and the foams made from it, ignitable propellantair mixtures can arise due to the diffusing propellant (pentane, LEL of 1.3 vol%). Therefore, adequate ventilation must be provided at all times.

All conceivable sources of ignition (naked flames, welding sparks, electrical sparks, etc.) must be kept away. Likewise, electrostatic charging must be avoided. A smoking ban must be observed at all costs!

Transport of Neopor® or freshly produced foams in unventilated or closed transport vehicles is not permitted. Further information can be found in the safety data sheet for the respective product.

#### **Biological effects**

Pentane escapes during storage and processing of Neopor<sup>®</sup>. Particularly when cutting the foams with heated wires, care must be taken to remove the resulting vapors, since they contain small amounts of styrene in addition to the pentane.

The regionally applicable occupational exposure limits for styrene and pentane must be observed.

#### Processing

Neopor® F 2000 is processed into foam in three stages. Further information can be found under **Product details**.

#### Pre-expansion

Neopor<sup>®</sup> F 2000 can be pre-expanded without difficulty using discontinuously operating, state of the art pre-expansion equipment.

For the production of particularly low bulk densities, double pre-expansion is recommended, with a conditioning time of 3-5 hours between the first and second pre-expansion steps.

#### Intermediate aging

The intermediate aging time must be selected depending on the bulk density and the prevailing ambient conditions. In general, the higher the bulk density, the longer the intermediate aging time.

### Molding

Depending on the bead size, Neopor® F 2000 can be moulded in commercially available block moulds or shape moulding machines. If regrind is added, make sure that the regrind density is as close as possible to the prepuff density to avoid separation of the regrind during further processing. It is recommended that the regrind be purified in advance in a dedusting system.

For further information on processing please contact your local BASF representative.

## Packaging for the finished products

Transparent films must **not** be used as packaging for Neopor<sup>®</sup> foams. The use of an opaque white or opaque colored film is strongly recommended.

## **Product details**

Product	Bead size class	Typical bead size	Typical pentane content	Typical application density
Neopor <sup>⊚</sup> F 2200	1.4-2.5mm	1.1 - 2.5 mm (≥ 94 %)	approx. 5.3%	12" - 25 kg/m <sup>3</sup>
Neopor® F 2300	0.8-1.4mm	0.6 - 1.6 mm (≥ 96 %)	approx. 5.3%	12" - 25 kg/m <sup>3</sup>
Neopor <sup>⊚</sup> F 2400	0.5-0.8mm	0.3 - 1.0 mm (≥ 96 %)	approx. 5.3%	16-24 kg/m <sup>3</sup>

Product	Achievable bulk density	Usual intermediate aging time	Typical applications
Neopor <sup>®</sup> F 2200	16kg/m³	10-48h	Exterior insulation (ETICS), blown cavity wall insulation
Neopor <sup>®</sup> F 2300	16kg/m³	10-48h	Exterior insulation (ETICS), roof, wall, floor and ceiling insulation, blown cavity wall insulation
Neopor <sup>⊛</sup> F 2400	16kg/m³	10-48h	Insulating boxes, formwork elements (ICF), technical mouldings

\* Density usually achievable by single pre-expansion in discontinuous, state of the art pre-expanders

\*\* by double pre-expansion

Further information on product properties and application of Neopor® can be found at www.neopor.de.

#### Note

The data contained in this publication are based on our current knowledge and experience. In view of the many factors that may affect processing and application of our product, these data do not relieve processors from carrying out their own investigations and tests; neither do these data imply any guarantee of certain properties, nor the suitability of the product for a specific purpose. Any descriptions, drawings, photographs, data, proportions, weights etc. given herein may change without prior information and do not constitute the agreed contractual quality of the product. It is the responsibility of the recipient of our products to ensure that any proprietary rights and existing laws and legislation are observed.